

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1303050010

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

M12 LED Machine Light Kit, 40.00mm Outer Diameter, 190.50mm Length, 5W

Documents:

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Portable Lighting
Series	130305
Connector End	Micro-Change® (M12)
IP Rating	IP67
NEMA Configuration	N/A
Outlet	None
Overview	Brad Micro-Change (M12) Connectors
Product Name	M12 LED Machine Light
Type	Ind Automation Machine Lights
UPC	78172558201

Physical	
Cord Length - Primary	5.0m (16.40')
Cord Length - Secondary	1.0m (3.28')
Depth	40.00mm (1.570")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	30.00mm (1.18")
Length	190.50mm (7.50")
Material - Guard	N/A
Mounting Style	Screw-Bracket
Packaging Type	Carton
Socket Construction	N/A

Electrical	
Bulb Type	LED - 5000K
Cord Type - Primary	22/5 WSOR
Cord Type - Secondary	22/5 WSOR
Lamp Type	LED
Lamp Wattage - Maximum	5W
Lumens	480
On/Off Switch	No
Voltage (Fixture) - Maximum	24V DC

Material Info	
Engineering Number	M12MXIS40-5W



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130305 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1303050010