

FEATURES

- * 4 inch (101.6 mm) MATRIX HEIGHT.
- * LOW POWER REQUIREMENT.
- * SINGLE PLANE, WIDE VIEWING ANGLE
- * SOLID STATE RELIABILITY.
- * 5x7 ARRAY WITH X-Y SELECT.
- * COMPATIBLE WITH USASCLL AND EBCDIC CODES.
- * STACKABLE HORIZONTALLY.
- * CATEGORIZED FOR LUMINOUS INTENSITY.


DESCRIPTION

The LTP-4257AA is a 4 inch (101.6 mm) matrix height 5x7 dot matrix display. This device is multicolor applicable display, which has gray face and white dot color. The red orange LED chip is made from GaAsP on a GaP substrate. The green LED chip is made from GaP on a GaP substrate.

DEVICE


PART NO.	DESCRIPTION
Red Orange & Green	Anode Column
LTP-4257AA	Cathode Row

PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerances are ± 0.25 mm (0.01") unless otherwise noted.

INTERNAL CIRCUIT DIAGRAM



THE SIGN "↑" STANDS FOR 2 RED ORANGE CHIPS IN SERIES.
THE SIGN "↓" STANDS FOR 2 GREEN CHIPS IN SERIES.

PIN CONNECTION

No	CONNECTION	No	CONNECTION
1	ANODE COLUMN 1 (GREEN)	15	ANODE COLUMN 5 (GREEN)
2	ANODE COLUMN 1 (RED ORANGE)	16	ANODE COLUMN 5 (RED ORANGE)
3	CATHODE ROW 7 (GREEN)	17	CATHODE ROW 1 (GREEN)
4	CATHODE ROW 7 (RED ORANGE)	18	CATHODE ROW 1 (RED ORANGE)
5	ANODE COLUMN 2 (GREEN)	19	ANODE COLUMN 4 (GREEN)
6	ANODE COLUMN 2 (RED ORANGE)	20	ANODE COLUMN 4 (RED ORANGE)
7	ANODE COLUMN 3 (GREEN)	21	ANODE COLUMN 3 (GREEN)
8	ANODE COLUMN 3 (RED ORANGE)	22	ANODE COLUMN 3 (RED ORANGE)
9	CATHODE ROW 5 (GREEN)	23	CATHODE ROW 3 (GREEN)
10	CATHODE ROW 5 (RED ORANGE)	24	CATHODE ROW 3 (RED ORANGE)
11	CATHODE ROW 4 (GREEN)	25	CATHODE ROW 4 (GREEN)
12	CATHODE ROW 4 (RED ORANGE)	26	CATHODE ROW 4 (RED ORANGE)
13	CATHODE ROW 6 (GREEN)	27	CATHODE ROW 2 (GREEN)
14	CATHODE ROW 6 (RED ORANGE)	28	CATHODE ROW 2 (RED ORANGE)

ABSOLUTE MAXIMUM RATING AT $T_A=25^\circ\text{C}$

PARAMETER	GREEN	RED ORANGE	UNIT
Average Power Dissipation Per Dot	64		mW
Peak Forward Current Per Dot	90		mA
Average Forward Current Per Dot	11		mA
Derating Linear From 25°C Per Dot	0.15		mA/ $^\circ\text{C}$
Reverse Voltage Per Dot	10		V
Operating Temperature Range	-35°C to $+85^\circ\text{C}$		
Storage Temperature Range	-35°C to $+85^\circ\text{C}$		
Solder Temperature 1/16 inch Below Seating Plane for 3 Seconds	260°C		

ELECTRICAL / OPTICAL CHARACTERISTICS AT $T_A=25^\circ\text{C}$

GREEN

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	2600	9600		μcd	$I_p=80\text{mA}$ 1/16DUTY
Peak Emission Wavelength	λ_p		565		nm	$I_F=20\text{mA}$
Spectral Line Half-Width	$\Delta\lambda$		30		nm	$I_F=20\text{mA}$
Dominant Wavelength	λ_d		569		nm	$I_F=20\text{mA}$
Forward Voltage any Dot	V_F		4.2	5.2	V	$I_F=20\text{mA}$
			6	7.4	V	$I_F=80\text{mA}$
Reverse Current any Dot	I_R			100	μA	$V_R=10\text{V}$
Luminous Intensity Matching Ratio	$I_v\text{-m}$			2:1		$I_p=80\text{mA}$ 1/16DUTY

RED ORANGE

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	2600	9600		μcd	$I_p=80\text{mA}$ 1/16DUTY
Peak Emission Wavelength	λ_p		630		nm	$I_F=20\text{mA}$
Spectral Line Half-Width	$\Delta\lambda$		40		nm	$I_F=20\text{mA}$
Dominant Wavelength	λ_d		621		nm	$I_F=20\text{mA}$
Forward Voltage any Dot	V_F		4	5.2	V	$I_F=20\text{mA}$
			5.2	6.8	V	$I_F=80\text{mA}$
Reverse Current any Dot	I_R			100	μA	$V_R=10\text{V}$
Luminous Intensity Matching Ratio	$I_v\text{-m}$			2:1		$I_p=80\text{mA}$ 1/16DUTY

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclairage) eye-response curve.

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig1. RELATIVE INTENSITY VS. WAVELENGTH




Fig2. RELATIVE LUMINOUS EFFICIENCY (LUMINOUS INTENSITY PER UNIT CURRENT) VS. PEAK CURRENT (REFRESH RATE 1KHz)




Fig3. FORWARD CURRENT VS. FORWARD VOLTAGE




Fig4. RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig5. MAX. AVERAGE FORWARD CURRENT VS. AMBIENT TEMPERATURE.




Fig6. MAX. PEAK CURRENT VS. DUTY CYCLE % (REFRESH RATE 1KHz)

NOTE: G=GREEN & E=RED ORANGE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lite-On:](#)

[LTP-4257AA](#)